



Ledinaire panel

RC065Z SMB W60L60

Finger-protected, 0.2 J standard, White

The Philips Ledinaire panel Gen5 (RC065B/RC066B) range features a selection of popular off-the-shelf LED luminaires that offer Philips high quality at a competitive price. Reliable, energy-efficient and affordable, this latest generation of 600 x 600 mm, 620 x 620 mm, 300 x 1200 mm, and 600 x 1200 Ledinaire LED panel lights are designed for diffuse, comfortable lighting in a wide range of general lighting applications. Our range of Ledinaire panels lighting is also available with accessories for easy installation on different types of ceilings—just what you need.

Product data

General Information	
Angle	-
Accessory color	White
Value ladder	Value
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Mechanical and Housing	
Overall length	613 mm
Overall width	613 mm
Overall height	72.5 mm
Dimensions (Height x Width x Depth)	73 x 613 x 613 mm
Material	Composite
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	-
Product Data	
Order product name	RC065Z SMB W60L60
Full product name	RC065Z SMB W60L60
Full product code	871016336272499
Order code	911401892480
Material Nr. (12NC)	911401892480
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163362724
Numerator - Packs per outer box	10
EAN/UPC - Case	8710163362793