



Coreline Slim Batten

BN126C LED60S/865 PSU L1500

Coreline Slim Batten, 46 W, 6000 lm, 6500 K

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

Product data

General Information		Temperature	
Light source engine type	LED	Ambient temperature range	-20 to +40 °C
CE mark	CE mark		
Light Technical		Controls and Dimming	
Luminous Flux	6,000 lm	Dimmable	No
Correlated Color Temperature (Nom)	6500 K	Control interface	-
Luminous Efficacy (rated) (Nom)	105 lm/W		
Color rendering index (CRI)	>80	Mechanical and Housing	
Light source color	865 cool daylight	Housing Material	Steel
Optical cover type	Polycarbonate Diffuser	Optical cover material	Polycarbonate
		Housing Color	White RAL 9003
		Optical cover finish	Opal
Operating and Electrical		Overall length	1,450 mm
Input Voltage	220 to 240 V	Overall width	65 mm
Line Frequency	50 or 60 Hz	Overall height	65 mm
Power Consumption	46 W	Dimensions (Height x Width x Depth)	65 x 65 x 1450 mm
Power Factor (Fraction)	0.9		
Number of products on MCB of 16 A type B	30	Approval and Application	
		Ingress protection code	IP20/40 [Finger-protected, Emitting surface]
		Mech. impact protection code	IK04 [0.5 J standard plus]

Coreline Slim Batten

Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BN126C LED60S/865 PSU L1500
Full product name	BN126C LED60S/865 PSU L1500
Full product code	692382863856699

Order code	911401899280
Material Nr. (12NC)	911401899280
Local order code	BN12660L8655FT
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828638566
Numerator - Packs per outer box	6
EAN/UPC - Case	6923828638627

Dimensional drawing

