



CityCurve gen2

BSP295 ECO43/740 PSR WSO II GR-900

CityCurve gen 2, LED EconomyLine 4300 lm, 740 neutral white, Power supply unit regulating, Safety class II, Wide street optic

Offering a contemporary interpretation of the old ‘bell’-shaped street light, CityCurve gen2, with its retro appearance, fits both modern urban spaces as well as historical environments. Its LED module allows cities to focus on reducing energy consumption. Designed for installation at heights of 4 to 6 meters, and offering a wide choice of brackets and columns, CityCurve gen2 is ideal for lighting urban centers and streets, pedestrian areas, squares and parks.

Product data

General Information		Optic type outdoor	
Lamp family code	ECO43 [LED EconomyLine 4300 lm]	Wide street optic	
Light source replaceable	Yes	Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Product family code	BSP295 [CityCurve gen 2]	Line Frequency	50 to 60 Hz
Lighting Technology	LED	Power Consumption	41 W
CE mark	Yes	Temperature	
ENEC mark	ENEC mark	Ambient temperature range	-25 to +35 °C
Glow-wire test	Temperature 650 °C, duration 5 s	Controls and Dimming	
Light Technical		Dimmable	Yes
Luminous Flux	3,269 lm	Driver/power unit/transformer	Power supply unit regulating
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	79.7 lm/W	Housing Material	Aluminum
Number of light sources	24	Optical cover material	Polycarbonate
Light source color	740 neutral white		
Optical cover type	Polycarbonate bowl/cover clear		

CityCurve gen2

Mounting device	Spigot
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Protection class IEC	Safety class II
Product Data	
Order product name	BSP295 ECO43/740 PSR WSO II GR-900
Full product name	BSP295 ECO43/740 PSR WSO II GR-900

Full product code	871794312024600
Order code	12024600
Material Nr. (12NC)	912300020025
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943120246
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943120246

Dimensional drawing

