



BSP295 GRN24/830 PSR WSO | GR-900

Offering a contemporary interpretation of the old 'bell'-shaped street light, CityCurve gen2, with its retro appearance, fits both modern urban spaces as well as historical environments. Its LED module allows cities to focus on reducing energy consumption. Designed for installation at heights of 4 to 6 meters, and offering a wide choice of brackets and columns, CityCurve gen2 is ideal for lighting urban centers and streets, pedestrian areas, squares and parks.

General Information	
Lamp family code	GRN24 [LED GreenLine 2400 lm]
Light source replaceable	Yes
Driver included	Yes
Product family code	BSP295 [CityCurve gen 2]
Lighting Technology	LED
CE mark	Yes
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s

Optical cover type	Polycarbonate bowl/cover clear
Optic type outdoor	Wide street optic

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	29 W

Ambient temperature range	-25 to +35 °C
---------------------------	---------------

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating

Housing Material	Aluminum
------------------	----------

CityCurve gen2

Optical cover material	Polycarbonate
Mounting device	Spigot

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Init. Color Rendering Index Tolerance	+/-2
---------------------------------------	------

Product Data

Order product name	BSP295 GRN24/830 PSR WSO I GR-900
--------------------	-----------------------------------

Full product name	BSP295 GRN24/830 PSR WSO I GR-900
Full product code	871794312025300
Order code	12025300
Material Nr. (12NC)	912300020026
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943120253
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943120253

Dimensional drawing

