



Metis diver unit

EGP400 10 PSD 40W DEC 10xOUT 2M20 2M20

Remote multi driver unit, Safety class I

LED drivers often need to be located outside the driving envelope, therefore only the LED units are mounted in the tunnel. This maximizes tunnel availability and minimizes the number of critical components of the lighting system inside the tunnel. The Metis driver unit was developed precisely for this purpose. It is a large enclosure with multiple drivers that power LED units from a remote position.

Product data

General Information	
Angle	0°
Accessory color	Black
Product family code	EGP400 [Remote multi driver unit]
CE mark	Yes
Operating and Electrical	
Input Voltage	220 to 230 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Overall length	1,155 mm
Overall width	355 mm
Overall height	155 mm
Dimensions (Height x Width x Depth)	155 x 355 x 1155 mm
Material	Aluminum

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I
Product Data	
Order product name	EGP400 10 PSD 40W DEC 10xOUT 2M20 2M20
Full product name	EGP400 10 PSD 40W DEC 10xOUT 2M20 2M20
Full product code	871869910981300
Order code	912300023790
Material Nr. (12NC)	912300023790
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699109813
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699109813