



CitySoul gen2 LED Mini

BVP530 LED60-4S/830 II DM50 D9 SRG10 AL

CitySoul gen2 Mini for dedicated br, LED module 6000 lm, 830 warm white, Power supply unit with DALI interface, Safety class II, Distribution medium 50, Clear glass, Grey, Luminaire surge protection level up to 10 kV differential mode and 10 kV common mode

CitySoul gen2 LED is one of the most versatile and inspirational urban street lighting families designed by Philips to date. This highly efficient range delivers excellent lighting levels whilst also providing the right ambiance for all urban application areas, from the outskirts of the city right through to the city center. By evolving the modularity of the CitySoul family and adding new innovations like the Lyre and the Accent bracket, Philips has made this range the ideal toolbox for every urban context. The design is flatter, completely round, and the transitions with the spigot and bracket entirely flush, thereby giving your cityscape a coherent, elegant and discreet identity. Designed around its LED engine, CitySoul gen2 LED is highly efficient and easy to maintain. It comes in two sizes and is suitable for side-entry, post-top, catenary and suspended mounting.

Product data

General Information		Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Lamp family code	LED60 [LED module 6000 lm]		
Light source replaceable	Yes		
Number of gear units	Unit	Light source engine type	LED
Driver included	Yes	Product family code	BVP530 [CitySoul gen2 Mini for dedicated br]

CitySoul gen2 LED Mini

Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical

Upwards light output ratio	0.03
Luminous Flux	5,100 lm
Standard tilt angle post-top	-
Standard tilt angle side entry	-
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	111 lm/W
Colour rendering index (CRI)	≥80
Light source colour	830 warm white
Optical cover type	Clear glass
Luminaire light beam spread	-
Optic type outdoor	Distribution medium 50

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	46 W
Power Factor (Fraction)	0.96
Connection	Screw connection block
Cable	-
Number of products on MCB of 16 A type B	11

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	Acrylate
Optic material	Polymethyl methacrylate
Optical cover/lens material	Glass
Fixation material	Aluminium

Housing Colour	Grey
Mounting device	-
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall height	95 mm
Overall diameter	540 mm
Effective projected area	0.054 m²

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L92

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%

Product Data

Order product name	BVP530 LED60-4S/830 II DM50 D9 SRG10 AL
Full product name	BVP530 LED60-4S/830 II DM50 D9 SRG10 AL
Full EOC	871869989206700
Order code	89206700
Material no. (12 NC)	912300024533
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8718699892067
Numerator – packs per outer box	1
EAN/UPC - Case	8718699892067

CitySoul gen2 LED Mini

Dimensional drawing

