



# iColor Flex LMX gen2

## BGC495 50 RGB CLFT4 WH

iColor Flex LMX gen2, Clear Flat Lens, White Housing, 4 in On-Center Node Spacing

When designers need high-brightness RGB direct-view accent lighting, or need to design creative low-resolution video displays, iColor Flex LMX gen2 provides flexible strands of large high-intensity LED nodes. Each Flex LMX gen2 node is individually controllable, providing ultimate flexibility of design.

### Product data

General Information	
Number of light sources	50 [ 50 pcs]
Lamp family code	LED-MD [ LED Multi-die]
Light source colour	RGB
Light source replaceable	Yes
Driver included	No
Optical cover/lens type	CLFT4 [ Clear flat 4 inch separated]
Luminaire light beam spread	105°
CE mark	CE mark
Light Technical	
Luminous intensity (peak value) on beam axis per node	11 cd
Operating and Electrical	
Input Voltage	24 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Polycarbonate
Optical cover/lens material	Polycarbonate
Colour	White
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	30 lm
Initial LED luminaire efficacy	30 lm/W
Initial input power	1 W
Over Time Performance (IEC Compliant)	
Lumen Maintenance 50% at 25 °C Calculated	100000

iColor Flex LMX gen2

Lumen Maintenance 50% at 25 °C Reported	60000
Lumen Maintenance 50% at 50 °C Calculated	100000
Lumen Maintenance 50% at 50 °C Reported	60000
Lumen Maintenance 70% at 25 °C Calculated	100000
Lumen Maintenance 70% at 25 °C Reported	60000
Lumen Maintenance 70% at 50 °C Calculated	100000
Lumen Maintenance 70% at 50 °C Reported	60000

Application Conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------


Product Data

Full product code	871829162308399
Order product name	BGC495 50 RGB CLFT4 WH

EAN/UPC – product	8718291623083
Order code	101-000077-02
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400130024
SAP net weight (piece)	0.980 kg
Commercial Code	101-000077-02
Catalogue number description	iColor Flex LMX gen2, Clear Flat Lens, White Housing, 4 in On-Center Node Spacing



Dimensional drawing



iColor Flex LMX gen2

