



Vaya Cove LP G2

Vaya Cove LP G2, 4000 K, 1219 mm (4 ft), UL/CE

Vaya Cove LP G2, 4000 K, 1219 mm (4 ft), UL/CE

Vaya Cove LP G2 is a reliable cost-effective LED luminaire offering crisp white light for interior use. Designed for linear cove and accent lighting applications this luminaire offers a very low profile and integrated connectors to eliminate socket shadows. Vaya Cove LP offers on/off control or dimming via the use of any standard 0-10 V or DALI dimming controller.

Product data

General information		Optical cover/lens material		Polycarbonate
Lamp family code	LED-HB [LED High Brightness]	Optical cover/lens finish		Clear
Beam angle of light source	110 °	Length		1200 mm
Light source colour	Cool white	Colour		White
Light source replaceable	No			
Driver included	No	Approval and application		
Luminaire light beam spread	110°	Ingress protection code		IP40 [Wire-protected]
CE mark	CE mark			
UL mark	UL and cUL mark	Initial performance (IEC compliant)		
		Initial luminous flux (system flux)		1116 lm
		Initial luminous flux at colour temperature of 4,000 K		1116 lm
		Initial LED luminaire efficacy		106 lm/W
		Init. Corr. Colour Temperature		4000 K
		Init. Colour rendering index		≥80
		Initial input power		10.6 W
		Over time performance (IEC compliant)		
		Lumen Maintenance 70% at 25 °C Calculated		100000
		Lumen Maintenance 70% at 25 °C Reported		60000

Vaya Cove LP G2

Lumen Maintenance 70% at 50 °C Calculated	100000
Lumen Maintenance 70% at 50 °C Reported	60000
Lumen Maintenance 80% at 25 °C Calculated	100000
Lumen Maintenance 80% at 25 °C Reported	60000
Lumen Maintenance 80% at 50 °C Calculated	97000
Lumen Maintenance 80% at 50 °C Reported	60000
Lumen Maintenance 90% at 25 °C Calculated	56000
Lumen Maintenance 90% at 25 °C Reported	56000
Lumen Maintenance 90% at 50 °C Calculated	45000
Lumen Maintenance 90% at 50 °C Reported	45000

Application conditions

Ambient temperature range	-20 to +50 °C
---------------------------	---------------


Product data

Full product code	871869921304699
-------------------	-----------------

Order product name	SM452L 4000 24V L1200 CE UL
EAN/UPC – product	8718699213046
Order code	350-000017-11
SAP numerator – quantity per pack	1
Numerator – packs per outer box	30
SAP material	912400135346
Net Weight (Piece)	0.330 kg
Commercial Code	350-000017-11
Catalogue number description	Vaya Cove LP G2, 4000 K, 1219 mm (4 ft), UL/CE



Dimensional drawing



SM452L 4000 24V L1200 CE UL

