



iColor Flex LMX gen2

iColor Flex LMX gen2, Narrow Beam Lens, Black Housing, 12 in On-Center Node Spacing

iColor Flex LMX gen2, Narrow Beam Lens, Black Housing, 12 in On-Center Node Spacing

When designers need high-brightness RGB direct-view accent lighting, or need to design creative low-resolution video displays, iColor Flex LMX gen2 provides flexible strands of large high-intensity LED nodes. Each Flex LMX gen2 node is individually controllable, providing ultimate flexibility of design.

Product data

General Information	
Number of light sources	50 [50 pcs]
Lamp family code	LED-MD [LED Multi-die]
Light source colour	RGB
Light source replaceable	Yes
Driver included	No
Optical cover/lens type	PC-UV [Polycarbonate bowl/cover UV-resistant]
Luminaire light beam spread	36°
CE mark	CE mark
Light Technical	
Luminous intensity (peak value) on beam axis per node	28.7 cd
Operating and Electrical	
Input Voltage	24 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Polycarbonate
Optical cover/lens material	Polycarbonate
Colour	Black
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	28 lm
Initial LED luminaire efficacy	27.9 lm/W
Initial input power	1 W

iColor Flex LMX gen2

Over Time Performance (IEC Compliant)

Lumen Maintenance 50% at 25 °C Calculated	100000
Lumen Maintenance 50% at 25 °C Reported	60000
Lumen Maintenance 50% at 50 °C Calculated	100000
Lumen Maintenance 50% at 50 °C Reported	60000
Lumen Maintenance 70% at 25 °C Calculated	56000
Lumen Maintenance 70% at 25 °C Reported	56000
Lumen Maintenance 70% at 50 °C Calculated	56000
Lumen Maintenance 70% at 50 °C Reported	56000

Application Conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------


Product Data

Full product code	871869921462399
-------------------	-----------------

Order product name	BGC495 50 RGB NRRW BK P305
EAN/UPC – product	8718699214623
Order code	101-000077-10
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400135779
SAP net weight (piece)	0.750 kg
Commercial Code	101-000077-10
Catalogue number description	iColor Flex LMX gen2, Narrow Beam Lens, Black Housing, 12 in On-Center Node Spacing

IP 66

Dimensional drawing



iColor Flex LMX gen2

