



# CitySoul poles and brackets

## JGP530 MBP-S 1000 76 RAL

Pole-mounting bracket 1 arm, RAL color

CitySoul gen2 is one of the most versatile and inspirational urban street lighting families designed by Philips to date. This highly efficient range delivers excellent lighting levels whilst also providing the right ambiance for all urban application areas, from the outskirts of the city right through to the city center. By evolving the modularity of the CitySoul family and adding new innovations like the Lyre and the Accent bracket, Philips has made this range the ideal toolbox for every urban context. The design is flatter, completely round, and the transitions with the spigot and bracket entirely flush, thereby giving your cityscape a coherent, elegant and discreet identity. Designed around its LED engine, CitySoul gen2 is highly efficient and easy to maintain. It comes in two sizes and is suitable for side-entry, post-top, catenary and suspended mounting.

### Product data

General Information		Overall diameter	
Bracket type	Pole-mounting bracket 1 arm	Overall diameter	76 mm
Bracket color	RAL color	Dimensions (Height x Width x Depth)	410 x 76 x 1038 mm
Value ladder	Specification	Bracket tilt angle	2°
CE mark	Yes	Bracket length	1000 mm
Mechanical and Housing		Product Data	
Fixation diameter	Mounting device diameter 76 mm	Order product name	JGP530 MBP-S 1000 76 RAL
Overall length	1,038 mm	Full product name	JGP530 MBP-S 1000 76 RAL
Overall width	76 mm	Full product code	871869693707500
Overall height	410 mm	Order code	912401451494
		Material Nr. (12NC)	912401451494

# CitySoul poles and brackets

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696937075
Numerator - Packs per outer box	1

EAN/UPC - Case	8718696937075
----------------	---------------

## Dimensional drawing

