



# CoreLine Recessed Spot

## RS140Z CFRM RND-ADJUST D80 BK

CoreLine Recessed Spot, Accessory, Aluminum, Black, 0.3 J, Finger-protected

CoreLine Recessed Spot delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. CoreLine Recessed Spot is a recessed spot range designed to replace halogen-based luminaires. Its halogen-like look and attractive price make it easier for customers to make the switch to LED. This product provides a natural lighting effect for accent lighting applications, as well as instant energy savings and much longer lifetime – an environmentally friendly solution. With the push-in connectors, installation is fast and straightforward.

### Product data

General Information		Approval and Application	
Accessory color	Black	Ingress protection code	IP20 [Finger-protected]
Value ladder	Performance	Mech. impact protection code	IK03 [0.3 J]
Protection class IEC		-	
Operating and Electrical		Product Data	
Input Voltage	- V	Order product name	RS140Z CFRM RND-ADJUST D80 BK
Line Frequency	- Hz	Full product name	RS140Z CFRM RND-ADJUST D80 BK
Mechanical and Housing		Full product code	871869938448799
Overall height	28.5 mm	Order code	912401483072
Overall diameter	95 mm	Material Nr. (12NC)	912401483072
Material	Aluminum	Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718699384487
		Numerator - Packs per outer box	18

## CoreLine Recessed Spot

---

EAN/UPC - Case	8718699384494
----------------	---------------

---

