

CoreLine Recessed Spot

RS140Z CFRM SQR-ADJUST WH

CoreLine Recessed Spot, Accessory, Aluminum, White, 0.3 J, Finger-protected

CoreLine Recessed Spot delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. CoreLine Recessed Spot is a recessed spot range designed to replace halogen-based luminaires. Its halogen-like look and attractive price make it easier for customers to make the switch to LED. This product provides a natural lighting effect for accent lighting applications, as well as instant energy savings and much longer lifetime – an environmentally friendly solution. With the push-in connectors, installation is fast and straightforward.

Product data

General Information	
Accessory color	White
Value ladder	Performance

Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz

Mechanical and Housing	
Overall length	95 mm
Overall width	95 mm
Overall height	28.8 mm
Dimensions (Height x Width x Depth)	29 x 95 x 95 mm
Material	Aluminum

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	-

Product Data	
Order product name	RS140Z CFRM SQR-ADJUST WH
Full product name	RS140Z CFRM SQR-ADJUST WH
Full product code	871869938456299
Order code	912401483134
Material Nr. (12NC)	912401483134
Numerator - Quantity Per Pack	1

CoreLine Recessed Spot

EAN/UPC - Product/Case	8718699384562
Numerator - Packs per outer box	18
EAN/UPC - Case	8718699384579

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.