



CoreLine Recessed Spot

RS140Z CFRM SQR-ADJUST ALU

CoreLine Recessed Spot, Accessory, Aluminum, Aluminum, 0.3 J, Finger-protected

CoreLine Recessed Spot delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. CoreLine Recessed Spot is a recessed spot range designed to replace halogen-based luminaires. Its halogen-like look and attractive price make it easier for customers to make the switch to LED. This product provides a natural lighting effect for accent lighting applications, as well as instant energy savings and much longer lifetime – an environmentally friendly solution. With the push-in connectors, installation is fast and straightforward.

Product data

General Information		Material	
Accessory color	Aluminum	Aluminum	
Value ladder	Performance		
Operating and Electrical		Approval and Application	
Input Voltage	- V	Ingress protection code	IP20 [Finger-protected]
Line Frequency	- Hz	Mech. impact protection code	IK03 [0.3 J]
		Protection class IEC	-
Mechanical and Housing		Product Data	
Overall length	95 mm	Order product name	RS140Z CFRM SQR-ADJUST ALU
Overall width	95 mm	Full product name	RS140Z CFRM SQR-ADJUST ALU
Overall height	28.8 mm	Full product code	871869938458699
Dimensions (Height x Width x Depth)	29 x 95 x 95 mm	Order code	912401483135
		Material Nr. (12NC)	912401483135
		Numerator - Quantity Per Pack	1

CoreLine Recessed Spot

EAN/UPC - Product/Case	8718699384586
Numerator - Packs per outer box	18
EAN/UPC - Case	8718699384593

