



CoreLine Recessed Spot

RS143Z CFRM GRID 1x2 WH

CoreLine Recessed Spot, Accessory, Aluminum, White, 0.3 J, Finger-protected

CoreLine Recessed Spot delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. CoreLine Recessed Spot is a recessed spot range designed to replace halogen-based luminaires. Its halogen-like look and attractive price make it easier for customers to make the switch to LED. This product provides a natural lighting effect for accent lighting applications, as well as instant energy savings and much longer lifetime – an environmentally friendly solution. With the push-in connectors, installation is fast and straightforward.

Product data

General Information		Material	
Accessory color	White	Aluminum	
Value ladder	Performance	Approval and Application	
Operating and Electrical		Ingress protection code	IP20 [Finger-protected]
Input Voltage	- V	Mech. impact protection code	IK03 [0.3 J]
Line Frequency	- Hz	Protection class IEC	-
Mechanical and Housing		Product Data	
Overall length	200 mm	Order product name	RS143Z CFRM GRID 1x2 WH
Overall width	110 mm	Full product name	RS143Z CFRM GRID 1x2 WH
Overall height	53 mm	Full product code	871869938833199
Dimensions (Height x Width x Depth)	53 x 110 x 200 mm	Order code	912401483213
		Material Nr. (12NC)	912401483213
		Numerator - Quantity Per Pack	1

CoreLine Recessed Spot

EAN/UPC - Product/Case	8718699388331
Numerator - Packs per outer box	12
EAN/UPC - Case	8718699388362

Dimensional drawing

