



Image
not
available

Platines Faible Puissance EGS350

EGS350 SON-T250W WV

EGS350 - SON-T - 250 W - Version large

A range of prewired foot pole gear trays is available for Road Lighting luminaires. A gear tray consists of a metal tray on which electrical components (capacitors, ballast, ignitor), wiring and terminal blocks are mounted. These gear trays are normally used in combination with Road luminaires, which cannot integrate electrical components because of lack of space or because of high temperatures.

Données du produit

Caractéristiques générales	
Nombre de sources lumineuses	1 [1 pc]
Code famille de lampe	SON-T [SON-T]
Puissance de la lampe	250 W
Classe de protection CEI	Classe de sécurité I
Marquage CE	Marquage CE
Marquage ENEC	Marquage ENEC
Code de la famille de produits	EGS350 [EGS350]
Caractéristiques électriques	
Tension d'entrée	230 V
Matériaux et finitions	
Configuration du boîtier	WV [Version large]
Dimensions (hauteur x largeur x profondeur)	NaN x NaN x NaN mm (NaN x NaN x NaN in)

Normes et recommandations	
Code d'indice de protection	IP21 [Protection des doigts, protection contre les gouttes]
Données logistiques	
Code de produit complet	871155916800500
Désignation Produit	EGS350 SON-T250W WV
Code barre produit (EAN)	8711559168005
Code de commande	16800500
Unité d'emballage	1
Conditionnement par carton	1
Code industriel (12NC)	913603140418
Poids net (pièce)	3,800 kg

Platines Faible Puissance EGS350

Schéma dimensionnel

Image
not
available

Gear EGS350

