
PHILIPS

Lighting



HID ignitors for series systems

SI 54 380-415V 50/60Hz

HID ignitors for series systems

Product data

Operating and Electrical	
Input Voltage	380 to 415 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Wiring	
Connector Type	Screw

Temperature	
Ambient temperature range	-20 °C to 75 °C
T-Case Maximum (Max)	80 °C


Mechanical and Housing	
Housing	SNI-115

Approval and Application	
Approval Marks	CE marking ENEC certificate

Product Data	
Order product name	SI 54 380-415V 50/60Hz
Full product name	SI 54 380-415V 50/60Hz
Full product code	871150091548130
Order code	913619149966
Material Nr. (12NC)	913619149966
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500915481
Numerator - Packs per outer box	20
EAN/UPC - Case	8711500908339

HID ignitors for series systems

Dimensional drawing



Product	D1	C1	A1	A2	B1
SI 54 380-415V 50/60Hz	4.3 mm	38.0 mm	114.5 mm	95.0 mm	41.0 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.