



Gear for SDW-T lamps

CSLS 50 SDW-T 220-240V 50/60HZ

CSLS electronic control unit with impregnated (HID 'BASIC') or encapsulated (HID 'Heavy Duty') electromagnetic ballasts

Avisos e Segurança

- Climatic suitability CSLS and HID BASIC: restricted to built in situations under normal conditions
- Climatic suitability CSLS and HID Heavy Duty: use in luminaires under humid conditions (not drip-proof)


Dados do produto

Funcionamento e características elétricas	
Tensão de entrada	220 a 240 V
Frequência de entrada	50 a 60 Hz
Cablagem	
Comprimento do cabo do dispositivo à lâmpada	0,50 m
Tipo de conector	Parafuso
Temperatura	
Vida útil da caixa T (Nom.)	90 °C
T-máxima na caixa (Máx.)	90 °C
Aprovação e aplicação	
Marcas de aprovação	Marca CE Certificação VDE-EMV Certificação CB

Dados do produto	
Nome de produto da encomenda	CSLS 50 SDW-T 220-240V 50/60Hz
Nome do produto completo	CSLS 50 SDW-T 220-240V 50/60HZ
Código do produto completo	871150090808730
Código de encomenda	90808730
N.º material (12NC)	913619179966
Numerador – Quantidade por embalagem	1
EAN/UPC - Produto/caixa	8711500908087
Numerador – Embalagens por caixa exterior	18
EAN/UPC - Caso	8711500908094

Gear for SDW-T lamps

Desenho dimensional



Product	D1	C1	A1	A2	B1	B2
CSLS 50 SDW-T 220-240V 50/60Hz	4,5 mm	39,5 mm	98,0 mm	70,0 mm	58,5 mm	46,0 mm

