

Gear for SDW-T lamps

CSLS 100 SDW-T 220-240V 50/60Hz

CSLS electronic control unit with impregnated (HID "BASIC") or encapsulated (HID "Heavy Duty") electromagnetic ballasts

Warnings and Safety

- Climatic suitability CSLS and HID BASIC: restricted to built in situations under normal conditions
- Climatic suitability CSLS and HID Heavy Duty: use in luminaires under humid conditions (not drip-proof)


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Wiring	
Cable Length From Device to Lamp	0.50 m
Connector Type	Screw
Temperature	
T-Case Lifetime (Nom)	90 °C
T-Case Maximum (Max)	90 °C
Approval and Application	
Approval Marks	CE marking VDE-EMV certificate CB Certificate

Product Data	
Order product name	CSLS 100 SDW-T 220-240V 50/60Hz
Full product name	CSLS 100 SDW-T 220-240V 50/60Hz
Full product code	871150090870430
Order code	90870430
Material Nr. (12NC)	913619189966
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500908704
Numerator - Packs per outer box	18
EAN/UPC - Case	8711500908711

Gear for SDW-T lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
CSLS 100 SDW-T 220-240V 50/60Hz	4.5 mm	39.5 mm	98.0 mm	70.0 mm	58.5 mm	46.0 mm

