



Sistem de control HID-CSLS pentru SDW

CSLS 100 SDW-T 220-240V 50/60Hz

Unitate de control electronică CSLS cu balasturi electromagnetice impregnate (HID "BASIC") sau încapsulate (HID "Heavy Duty")

Warnings and safety

- Climatic suitability CSLS and HID BASIC: restricted to built in situations under normal conditions
- Climatic suitability CSLS and HID Heavy Duty: use in luminaires under humid conditions (not drip-proof)


Catalog de date

Funcționare și sistem electric	
Tensiune de intrare	De la 220 până la 240 V
Frecvență de intrare	De la 50 până la 60 Hz
Cablaj	
Lungime cablu de la dispozitiv la lampă	0,50 m
Tip conector	Șurub
Temperatură	
Durată de viață T-case (nom.)	90 °C
Maximum T-case (max.)	90 °C
Aprobare și aplicație	
Mărci de omologare	Marcaj CE Certificat VDE-EMV Certificat CB

Date despre produs	
Nume comandă produs	CSLS 100 SDW-T 220-240V 50/60Hz
Numele complet al produsului	CSLS 100 SDW-T 220-240V 50/60Hz
Full EOC	871150090870430
Cod de comandă	90870430
Număr material (12NC)	913619189966
Numărător SAP – Cantitate per pachet	1
EAN/UPC – Produs/Cutie	8711500908704
Numărător SAP – Pachete per exterior	18
EAN/UPC – Cutie	8711500908711

Sistem de control HID-CSLS pentru SDW

Cote



Product	D1	C1	A1	A2	B1	B2
CSLS 100 SDW-T 220-240V 50/60Hz	4,5 mm	39,5 mm	98,0 mm	70,0 mm	58,5 mm	46,0 mm

