



# HID ignitors for series systems

## SN 59 220-240V 50/60HZ

HID ignitors for series systems


### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Wiring	
Connector type	Screw
Temperature	
Ambient temperature range	-20°C to 75°C
T-Case maximum (max.)	80 °C
Mechanical and Housing	
Housing	SNI-115
Approval and Application	
Approval marks	CE marking ENEC certificate

Product Data	
Order product name	SN 59 220-240V 50/60Hz
Full product name	SN 59 220-240V 50/60HZ
Full EOC	871150091557330
Local code description	SN59
Order code	91557330
Material no. (12 NC)	913619659966
Local order code	SN59
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500915573
Numerator – packs per outer box	20
EAN/UPC - Case	8711500913487

# HID ignitors for series systems

## Dimensional drawing



Product	D1	C1	A1	A2	B1
SN 59 220-240V 50/60Hz	4.3 mm	38.0 mm	114.5 mm	95.0 mm	41.0 mm

