

HID-Constant wattage BSX for SOX

BSX 131 H96 220-240V 50Hz CW-178/78

Constant-wattage (potted) electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps


Product data

| Operating and Electrical | |
|--------------------------|-------------------------------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 Hz |
| Input frequency | 50 Hz |
| | |
| Wiring | |
| Connector type | Screw |
| | |
| Approval and Application | |
| Approval marks | CE marking ENEC certificate |
| | |
| Product Data | |
| Order product name | BSX 131 H96 220-240V 50Hz CW-178/78 |

| | |
|-----------------------------------|-------------------------------------|
| Full product name | BSX 131 H96 220-240V 50Hz CW-178/78 |
| Full EOC | 871150091978699 |
| Order code | 91978699 |
| Material no. (12 NC) | 913647057226 |
| Local order code | BSX131H96 |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC — Product/Case | 8711500919786 |
| Numerator – packs per outer box | 4 |
| EAN/UPC - Case | 8711500932204 |

HID-Constant wattage BSX for SOX

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 | B2 |
|--|--------|---------|----------|----------|----------|---------|
| BSX 131 H96 220-240V 50Hz CW-178/78 | 4.2 mm | 74.0 mm | 178.0 mm | 162.0 mm | 100.0 mm | 42.0 mm |

