



HID-Constant wattage BSX for SOX

BSX 131 H96 220-240V 50Hz CW-178/78

Constant-wattage (potted) electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BSX 131 H96 220-240V 50Hz CW-178/78

Full product name	BSX 131 H96 220-240V 50Hz CW-178/78
Full product code	871150091978699
Order code	913647057226
Material Nr. (12NC)	913647057226
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500919786
Numerator - Packs per outer box	4
EAN/UPC - Case	8711500932204

HID-Constant wattage BSX for SOX

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
BSX 131 H96 220-240V 50Hz CW-178/78	4.2 mm	74.0 mm	178.0 mm	162.0 mm	100.0 mm	42.0 mm

