

HID-HeavyDuty BSX for SOX

BSX 90 L40 230V 50Hz HD1-118

Encapsulated electromagnetic copper/iron ballasts for SOX and SOX-E lamps

Product data


Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BSX 90 L40 230V 50Hz HD1-118

Full product name	BSX 90 L40 230V 50Hz HD1-118	
Full product code	871150091993931	
Order code	913650080426	
Material Nr. (12NC)	913650080426	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8711500919939	
Numerator - Packs per outer box	6	
EAN/UPC - Case	8711500061867	

Datasheet, 2023, September 4 data subject to change

HID-HeavyDuty BSX for SOX

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSX 90 L40 230V 50Hz HD1-118	6.2 mm	53.0 mm	118.0 mm	103.0 mm	65.0 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.