



HID ignitors for series systems

SX 70 220-240V 50/60HZ

HID ignitors for series systems


Product data

| Operating and Electrical | |
|---------------------------|-----------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Input frequency | 50 to 60 Hz |
| Wiring | |
| Connector type | Screw |
| Temperature | |
| Ambient temperature range | -20 °C to 75 °C |
| T-Case maximum (max.) | 80 °C |
| Mechanical and Housing | |
| Housing | SNI-115 |

| Approval and Application | |
|-----------------------------------|-----------------------------|
| Approval marks | CE marking ENEC certificate |
| Product Data | |
| Order product name | SX 70 220-240V 50/60Hz |
| Full product name | SX 70 220-240V 50/60HZ |
| Full EOC | 871150091549830 |
| Order code | 91549830 |
| Material no. (12 NC) | 913654039066 |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8711500915498 |
| Numerator – packs per outer box | 20 |
| EAN/UPC - Case | 8711500914378 |

HID ignitors for series systems

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|------------------------|--------|---------|----------|---------|---------|
| SX 70 220-240V 50/60Hz | 4.3 mm | 38.0 mm | 114.5 mm | 95.0 mm | 41.0 mm |

