



# HID-Constant wattage BSX for SOX

## BSX 135 H96 220-240V 50Hz CW-149/67

Constant-wattage (potted) electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps


### Product data

Operating and Electrical	
Input Voltage	230 to 240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BSX 135 H96 220-240V 50Hz CW-149/67

Full product name	BSX 135 H96 220-240V 50Hz CW-149/67
Full product code	871150092007299
Order code	913654097226
Material Nr. (12NC)	913654097226
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500920072
Numerator - Packs per outer box	8
EAN/UPC - Case	8711500932228

# HID-Constant wattage BSX for SOX

## Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
BSX 135 H96 220-240V 50Hz CW-149/67	4.2 mm	67.0 mm	149.0 mm	135.0 mm	80.0 mm	42.0 mm

