



Image
not
available

Platines Faible Puissance EGS350

EGS350 2xSON-T250W LV

EGS350 - 2 pcs - SON-T - 250 W - Version longue

A range of prewired foot pole gear trays is available for Road Lighting luminaires. A gear tray consists of a metal tray on which electrical components (capacitors, ballast, ignitor), wiring and terminal blocks are mounted. These gear trays are normally used in combination with Road luminaires, which cannot integrate electrical components because of lack of space or because of high temperatures.

Données du produit

Caractéristiques générales	
Nombre de sources lumineuses	2 [2 pcs]
Code famille de lampe	SON-T [SON-T]
Puissance de la lampe	250 W
Classe de protection CEI	Classe de sécurité I
Marquage CE	Marquage CE
Marquage ENEC	Marquage ENEC
Code de la famille de produits	EGS350 [EGS350]

Caractéristiques électriques	
Tension d'entrée	230 V

Matériaux et finitions	
Configuration du boîtier	LV [Version longue]
Dimensions (hauteur x largeur x profondeur)	NaN x NaN x NaN mm (NaN x NaN x NaN in)

Normes et recommandations	
Code d'indice de protection	IP21 [Protection des doigts, protection contre les gouttes]

Données logistiques	
Code de produit complet	871155916870800
Désignation Produit	EGS350 2xSON-T250W LV
Code barre produit (EAN)	8711559168708
Code de commande	16870800
Unité d'emballage	1
Conditionnement par carton	1
Code industriel (12NC)	913666000418
Poids net (pièce)	7,000 kg



Platines Faible Puissance EGS350

Schéma dimensionnel

Image
not
available

Gear EGS350

