



HID ignitors for series systems

SND 58 220-240V 50/60Hz

HID ignitors for series systems


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Wiring	
Connector Type	Screw
Temperature	
Ambient temperature range	-20 °C to 85 °C
T-Case Maximum (Max)	90 °C
Mechanical and Housing	
Housing	SNI-85

Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	SND 58 220-240V 50/60Hz
Full product name	SND 58 220-240V 50/60Hz
Full product code	871150093068230
Order code	913700185166
Material Nr. (12NC)	913700185166
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500930682
Numerator - Packs per outer box	48
EAN/UPC - Case	8711500930699

HID ignitors for series systems

Dimensional drawing



Product	D1	C1	A1	A2	B1
SND 58 220-240V 50/60Hz	4.3 mm	38.5 mm	84.5 mm	65.0 mm	41.5 mm

