

# HID-Basic BSX for SOX

## BSX 35/55 L82 240V 50Hz BC0-196


Impregnated electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps

### Product data

Operating and Electrical		Full product name	
Input Voltage	240 V	Full product code	871150092053930
Line Frequency	50 Hz	Order code	913700200926
Input Frequency	50 Hz	Material Nr. (12NC)	913700200926
Wiring		Numerator - Quantity Per Pack	1
Connector Type	Insert	EAN/UPC - Product/Case	8711500920539
Approval and Application		Numerator - Packs per outer box	24
Approval Marks	CE marking ENEC certificate	EAN/UPC - Case	8711500944115
Product Data			
Order product name	BSX 35/55 L82 240V 50Hz BC0-196		

## HID-Basic BSX for SOX

### Dimensional drawing



Product	D1	C1	C3	A1	A2	A3	A4	B1	B2
BSX 35/55	4.2	28.0	1.5	196.0	180.0	54.0	54.0	39.0	20.0
L82 240V	mm	mm	mm	mm	mm	mm	mm	mm	mm
50Hz									
BC0-196									

