



# HID-HighPower for SON/MH/HPL/HPI

## BSN 1000 L78-A2 230/240V 50Hz HP-257

Encapsulated ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above


### Product data

<b>Operating and Electrical</b>	
Input Voltage	230 V (default) or 240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
<b>Wiring</b>	
Connector Type	Screw
<b>Approval and Application</b>	
Approval Marks	CE marking ENEC certificate
<b>Product Data</b>	
Order product name	BSN 1000 L78-A2 230/240V 50Hz HP-257

Full product name	BSN 1000 L78-A2 230/240V 50Hz HP-257
Full product code	871150006236900
Order code	913700217503
Material Nr. (12NC)	913700217503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500996640
Numerator - Packs per outer box	1
EAN/UPC - Case	8711500062369

# HID-HighPower for SON/MH/HPL/HPI

## Dimensional drawing



Product	D1	C1	A1	A2	A3	B1	B2
BSN 1000 L78-A2	6.5	102.0	257.0	222.0	246.0	117.0	88.0
230/240V 50Hz	mm	mm	mm	mm	mm	mm	mm
HP-257							

