

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 400 L33-TS 230V 50Hz HD3-166

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps (no ignitor needed for SON-I lamps)


Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BSN 400 L33-A2-TS 230V 50Hz HD3-166

Full product name	BSN 400 L33-TS 230V 50Hz HD3-166
Full product code	871150005976530
Order code	05976530
Material Nr. (12NC)	913700226926
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500059765
Numerator - Packs per outer box	4
EAN/UPC - Case	8711500059772

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 400 L33-A2-TS 230V 50Hz	6.2 mm	84.0 mm	166.0 mm	147.5 mm	102.0 mm
HD3-166					

