



# HID-High Power Basic for SON/MH/HPL

## BMH 2000 L5018-A

Basic aluminum/iron ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above• Basic aluminum/iron ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above


### Product data

Operating and Electrical	
Input Voltage	380 to 415 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BMH 2000 L5018-A2-A

Full product name	BMH 2000 L5018-A
Full product code	871829111851000
Order code	11851000
Material Nr. (12NC)	913700275326
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291118510
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291118527

# HID-High Power Basic for SON/MH/HPL

## Dimensional drawing



Product	D1	C1	A1	A2	A3	B1	B2
BMH 2000	6.5 mm	111.0	317.0	284.0	317.0	126.0	106.0
L5018-A2-A		mm	mm	mm	mm	mm	mm

