



HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

BSN 400 K407-ITS 230/240V 50Hz BC3-166


Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name		BSN 400 K407-ITS 230/240V 50Hz BC3-166	
Input Voltage	230 V (default) or 240 V	Full product code		872790088704400	
Line Frequency	50 Hz	Order code		88704400	
Input Frequency	50 Hz	Material Nr. (12NC)		913700277826	
		Numerator - Quantity Per Pack		1	
		EAN/UPC - Product/Case		8711500881571	
		Numerator - Packs per outer box		2	
		EAN/UPC - Case		8727900887044	
Approval and Application					
Approval Marks	CE marking ENEC certificate				
Product Data					
Order product name	BSN 400 K407-A2-ITS 230/240V 50Hz BC3				

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
BSN 400 K407-A2-ITS 230/240V 50Hz BC3	6.5 mm	83.0 mm	166.0 mm	145.0 mm	97.0 mm	78.5 mm

