



HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

BSN 400 K407-ITS 230/240V 50Hz BC3-166

Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data


Operating and Electrical					
Input Voltage	230 V (default) or 240 V				
Line Frequency	50 Hz				
Input Frequency	50 Hz				
Wiring					
Connector Type	Screw				
Approval and Application					
Approval Marks	CE marking ENEC certificate				
Product Data					
Order product name	BSN 400 K407-A2-ITS 230/240V 50Hz BC3				

Full product name	BSN 400 K407-ITS 230/240V 50Hz BC3-166			
Full product code	872790088704400			
Order code	88704400			
Material Nr. (12NC)	913700277826			
Numerator - Quantity Per Pack	1			
EAN/UPC - Product/Case	8711500881571			
Numerator - Packs per outer box	2			
EAN/UPC - Case	8727900887044			

Datasheet, 2023, April 15 data subject to change

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
BSN 400 K407-A2-ITS	6.5 mm	83.0 mm	166.0 mm	145.0 mm	97.0 mm	78.5 mm
230/240V 50Hz BC3						



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.