



HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

BSN 400 K407-ITS 230/240V 50Hz BC3-166

Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps


Product data

Operating and Electrical	
Input Voltage	230 V (default) or 240 V
Line Frequency	50 Hz
Input frequency	50 Hz
Wiring	
Connector type	Screw
Approval and Application	
Approval marks	CE marking ENEC certificate
Product Data	
Order product name	BSN 400 K407-A2-ITS 230/240V 50Hz BC3

Full product name	BSN 400 K407-ITS 230/240V 50Hz BC3-166
Full EOC	872790088704400
Order code	88704400
Material no. (12 NC)	913700277826
Local order code	BSN400K407ITS
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8711500881571
Numerator – packs per outer box	2
EAN/UPC - Case	8727900887044

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
BSN 400 K407-A2-ITS	6.5 mm	83.0 mm	166.0 mm	145.0 mm	97.0 mm	78.5 mm
230/240V 50Hz BC3						

