



HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

BSN 400 K407-A2-ITS 230/240V 50Hz BC3


Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name	BSN 400 K407-A2-ITS 230/240V 50Hz BC3
Input Voltage	230 V (default) or 240 V	Full product code	872790088704400
Line Frequency	50 Hz	Order code	913700277826
Input Frequency	50 Hz	Material Nr. (12NC)	913700277826
Wiring		Numerator - Quantity Per Pack	1
Connector Type	Screw	EAN/UPC - Product/Case	8711500881571
Approval and Application		Numerator - Packs per outer box	2
Approval Marks	CE marking ENEC certificate	EAN/UPC - Case	8727900887044
Product Data			
Order product name	BSN 400 K407-A2-ITS 230/240V 50Hz BC3		

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
BSN 400 K407-A2-ITS 230/240V 50Hz BC3	6.5 mm	83.0 mm	166.0 mm	145.0 mm	97.0 mm	78.5 mm

