



HID-Basic BHL MK4 for HPL/HPI

BHL 400 K307-A2 230/240V 50Hz BC2-160


Impregnated electromagnetic copper/iron ballasts for HPL, HPI (Plus) and SON-H lamps

Product data

Operating and Electrical		Full product name	BHL 400 K307-A2 230/240V 50Hz BC2-160
Input Voltage	230 V (default) or 240 V	Full product code	872790088703700
Line Frequency	50 Hz	Order code	913700278226
Input Frequency	50 Hz	Material Nr. (12NC)	913700278226
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500881595
		Numerator - Packs per outer box	6
		EAN/UPC - Case	8727900887037
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking ENEC certificate		
Product Data			
Order product name	BHL 400 K307-A2 230/240V 50Hz BC2-160		

HID-Basic BHL MK4 for HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 400 K307-A2 230/240V 50Hz	6.2 mm	65.0 mm	160.0 mm	139.0 mm	76.0 mm
BC2-160					

