



HF-Matchbox Blue

HF-M BLUE 121 LH TL5 230-240V

Compact, lightweight, High Frequency electronic ballast for TL (4-18W), TL5 (14-28W) and compact fluorescent PL (5-24W) lamps


Product data

Operating and Electrical	
Input Voltage	230 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Number of Products on MCB (16A Type B) (Nom)	59
Wiring	
Connector Type Input Terminals	Insert
Color Input Terminals	Gray
Color Output Terminals	Grey
Connector Type Output Terminals	Insert
Cable Length From Device to Lamp	1.50 m
Temperature	
Ambient temperature range	-10 °C to 40 °C
T-Case Maximum (Max)	75 °C
Mechanical and Housing	
Housing	LH

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Approval Marks	F-Marking CE marking VDE certificate CB Certificate
Product Data	
Order product name	HF-M BLUE 121 LH TL5 230-240V
Full product name	HF-M BLUE 121 LH TL5 230-240V
Full product code	871150053646430
Order code	53646430
Material Nr. (12NC)	913700418366
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500536464
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500536471

HF-Matchbox Blue

Dimensional drawing



Product	A1	A2	B1	C1	D1
HF-M BLUE 121 LH TL5 230-240V	187 mm	180 mm	22 mm	22 mm	4.4 mm

Product
HF-M BLUE 121 LH TL5 230-240V

