

HF-Matchbox Blue

HF-M BLUE 109 LH TL/PL-S 230-240V

HF-Matchbox Blue is an affordable, reliable, compact, lightweight and high-frequency ballast for use with system wattages below 25 W in combination with TL mini, TL-D, TL5 and TL5c, PL-T/C, and PL-L/S lamps. The HF-M Blue range has a robust design, meets all relevant international safety and performance standards and has an energy efficiency index (CELMA EEI) of A2.


Product data

Operating and Electrical	
Input Voltage	230 to 240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Number of products on MCB (16 A type B) (nom.)	159
Wiring	
Connector type input terminals	Insert
Colour input terminals	Blue
Colour output terminals	Grey
Connector type output terminals	Insert
Cable length from device to lamp	1.50 m
Temperature	
Ambient temperature range	-10°C to 40°C
T-Case maximum (max.)	75 °C
Mechanical and Housing	
Housing	LH

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Approval marks	F-Marking CE marking VDE certificate CB certificate
Product Data	
Order product name	HF-M BLUE 109 LH TL/PL-S 230-240V
Full product name	HF-M BLUE 109 LH TL/PL-S 230-240V
Full EOC	871150053680830
Order code	53680830
Material no. (12 NC)	913700421366
Local order code	HFMBLUE109LH
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500536808
Numerator – packs per outer box	50
EAN/UPC - Case	8711500536815

HF-Matchbox Blue

Dimensional drawing



Product	A1	A2	B1	C1	D1
HF-M BLUE 109 LH TL/PL-S 230-240V	144 mm	133 mm	22 mm	22 mm	4.2 mm

Product
HF-M BLUE 109 LH TL/PL-S 230-240V

