**PHILIPS** Lighting



# Core & Coil (71A) HPS 200W - 400W

## CORE & COIL HID HPS BAL 400W S51 120/220-240V 50HZ C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

#### **Product data**

General Information	
ANSI Code	S51-M169
Lamp Type	400W HPS
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A84N3
Core Size	4 x 4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI501-H4
Ignitor Temperature Rating	105°C
Capacitor Value	64 MFD
Capacitor Catalog Number	7C640S28RA
Capacitor Requirements	240V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	2.05 in
Capacitor Height	5 in
Automatic Restart	No

Operating and Electrical					
Input Voltage	120/230 V				
Input Frequency	50 Hz				
Input Current (Open Circuit)	1.9/1 A				
Input Current (Starting)	3.7/1.85 A				
Input Current (Short Circuit)	5.4-8.1/2.7-4.2 A				
Secondary Short Circuit Current	9.8-12.1 A				
Constant Wattage Deviation	Within Trapezoid				
Ballast Factor (Nom)	1				
Power Factor (Nom)	0.90				
Open Circuit Voltage	190 V				
Input Current (Nom)	4/2 A A				
Input Power (Nom)	465 W				
Rated Lamp Power	400 W				
Wiring					
Wire Striplength	0.5 mm				
Wire Length by Color	12"				
Wire Type	Stranded				
Remote Wiring Configuration Allowed	Yes				

### Core & Coil (71A) HPS 200W - 400W

Max Ballast-Lamp Distance Remote Wiring 2'					
Recommended Fuse Value	10/6 A				
Approval and Application					
Open Circuit Voltage Test (Volts)	175-215 V				
Approval Marks	RoHS Compliant				
Temperature Marking	D/D				
UL Recognized	Yes				
Hipot Test (1 Minute)	2000 V				
Hipot Test (2 Seconds)	2500 V				
UL Insulation Class	H(180°C)				
UL Temperature Code	1029D				

Product Data						
Order product name	CORE & COIL HID HPS BAL 400W S51					
	120/220-240V 50HZ C&C					
EAN/UPC - Product	781087043073					
Order code	913700505991					
Numerator - Quantity Per Pack	1					
Numerator - Packs per outer box	2					
Material Nr. (12NC)	913700505991					
Net Weight (Piece)	6.891 kg					

#### Dimensional drawing



HPS BAL 400W S51 120/220-240V 50HZ C&C

Pro	oduct	C1	C2	A1	A2	B1	B2
CO	RE & COIL HID HPS BAL 400W S51	4.1 in	2.5 in	4.8 in	4.4 in	4.3 in	3.9 in
120	/220-240V 50HZ C&C						



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2019, March 22 - data subject to change