



PrimaVision Mini for CDM

HID-PV m 1x020/I mCDM LPF 220-240V

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

Product data


Operating and Electrical			
Input Voltage	220 to 240 V		
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		
Earth Leakage Current (Max)	0.25 mA		
Inrush Current Width	0.40 ms		
Inrush Current Peak (Max)	30 A		
Number of Products on MCB (16A Type B)	48		
(Nom)			
Wiring			
Cable Length From Device to Lamp	2 m		
Connector Type	Insert		
Temperature			
Ambient temperature range	-20 °C to 50 °C		
T-Case Lifetime (Nom)	65 °C		
T-Case Maximum (Max)	75 °C		


Mechanical and Housing	
Housing	/I
Approval and Application	
Approval Marks	F-Marking CE marking CB Certificate
Product Data	
Order product name	HID-PV m PGJ5 20 /I CDM LPF 220-240V
Full product name	HID-PV m 1x020/I mCDM LPF 220-240V
Full product code	871150090981730
Order code	90981730
Material Nr. (12NC)	913700601666
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500909817
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500909824

Datasheet, 2023, April 16 data subject to change

PrimaVision Mini for CDM

Dimensional drawing





Product	D1	C1	A1	A2	B1
HID-PV m PGJ5 20 /I CDM LPF	4.2 mm	30.0 mm	190.0 mm	154.0 mm	43.3 mm
220-240V					

