



PrimaVision Mini for CDM

HID-PV m 1x020/I mCDM LPF 220-240V



Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

Product data

Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing	/I
Line Frequency	50 to 60 Hz		
Input frequency	50 to 60 Hz	Approval and Application	
Earth leakage current (max.)	0.25 mA	Approval marks	F-Marking CE marking CB Certificate
Inrush current width	0.40 ms		
Inrush current peak (max.)	30 A	Product Data	
Number of products on MCB (16 A type B) (nom.)	48	Order product name	HID-PV m PGJ5 20 /I CDM LPF 220-240V
		Full product name	HID-PV m 1x020/I mCDM LPF 220-240V
		Full EOC	871150090981730
		Order code	90981730
		Material no. (12 NC)	913700601666
		Local order code	HIDPVMPGJ5020I
		SAP numerator – quantity per pack	1
		EAN/UPC – Product/Case	8711500909817
		Numerator – packs per outer box	12
		EAN/UPC - Case	8711500909824
Wiring			
Cable length from device to lamp	2 m		
Connector type	Insert		
Temperature			
Ambient temperature range	-20 °C to 50 °C		
T-case lifetime (nom.)	65 °C		
T-Case maximum (max.)	75 °C		

PrimaVision Mini for CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV m PGJ5 20 /I CDM LPF 220-240V	4.2 mm	30.0 mm	190.0 mm	154.0 mm	43.3 mm

