



# PrimaVision Power for CDM

## HID-PV C 150 /S CDM 220-240V 50/60Hz


PrimaVision Power gear is designed for optimal performance of 100 and 150 W CDM lamps – ideal where high-intensity light is key.

### Product data

Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing	/S
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz	Approval and Application	
Earth Leakage Current (Max)	0.35 mA	Approval Marks	F-Marking CE marking VDE certificate VDE-EMV certificate CB Certificate
Inrush Current Width	.50 ms		
Inrush Current Peak (Max)	50 A	Product Data	
Number of Products on MCB (16A Type B) (Nom)	6	Order product name	HID-PV C 150 /S CDM 220-240V 50/60Hz
		Full product name	HID-PV C 150 /S CDM 220-240V 50/60Hz
		Full product code	871150091052330
		Order code	913700614066
		Material Nr. (12NC)	913700614066
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500910523
		Numerator - Packs per outer box	12
		EAN/UPC - Case	8711500910530
Wiring			
Cable Length From Device to Lamp	2.0 m		
Connector Type	Insert		
Temperature			
Ambient temperature range	-20 °C to 60 °C		
T-Case Lifetime (Nom)	75 °C		
T-Case Maximum (Max)	85 °C		

PrimaVision Power for CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV C 150 /S CDM 220-240V 50/60Hz	4.8 mm	32.0 mm	135.0 mm	123.5 mm	75.0 mm	63.5 mm

