



EXC for SOX

EXC 36 SOX-E 220-240V 50/60HZ

Electronic drivers for SOX lamps; designed to save energy and reduce maintenance costs

Product data


Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Inrush current width	0.15 ms
Input current (nom.)	0.17 A
Inrush current peak (max.)	30 A
Number of products on MCB (16 A type B)	30
(nom.)	
Wiring	
Cable length from device to lamp	5 m
Connector type	Insert
Temperature	
Ambient temperature range	-20°C to 50°C
T-case lifetime (nom.)	75 °C
Mechanical and Housing	
Housing	L 280x39x28

Approval and Application	
Safety standard	EN60928, 60926
Environmental standard	ISO 14001
Approval marks	CE marking ENEC certificate CB
	Certificate
Product Data	
Order product name	EXC 36 SOX-E 220-240V 50/60Hz
Full product name	EXC 36 SOX-E 220-240V 50/60HZ
Full EOC	871150006240630
Order code	06240630
Material no. (12 NC)	913700621566
Local order code	EXC036S50
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8711500062406
Numerator – packs per outer box	25
EAN/UPC - Case	8711500062413
	·

Datasheet, 2023, April 30 data subject to change

EXC for SOX

Dimensional drawing



 Product
 D1
 C1
 A1
 A2
 B1

 EXC 36 SOX-E 220-240V 50/60Hz
 4.2 mm
 28.0 mm
 280.0 mm
 265.0 mm
 40.0 mm

