



EXC for SOX

EXC 55 SOX 220-240V 50/60Hz

Electronic drivers for SOX lamps; designed to save energy and reduce maintenance costs

Product data


Operating and Electrical			
Input Voltage	220 to 240 V		
Line Frequency	50 to 60 Hz		
Input frequency	50 to 60 Hz		
Inrush current width	0.15 ms		
Input current (nom.)	0.26 A		
Inrush current peak (max.)	40 A		
Number of products on MCB (16 A type B)	22		
(nom.)			
Wiring			
Cable length from device to lamp	10 m		
Connector type	Insert		
Temperature			
Ambient temperature range	-20 °C to 50 °C		
T-case lifetime (nom.)	75 ℃		
Mechanical and Housing			
Housing	L 280x39x28		

Approval and Application				
Safety standard	EN60928, 60926			
Environmental standard	ISO 14001			
Approval marks	CE marking ENEC certificate CB Certificat			
Product Data				
Order product name	EXC 55 SOX 220-240V 50/60Hz			
Full product name	EXC 55 SOX 220-240V 50/60Hz			
Full EOC	871150006242030			
Order code	06242030			
Material no. (12 NC)	913700621666			
SAP numerator – quantity per pack	1			
EAN/UPC — Product/Case	8711500062420			
Numerator – packs per outer box	25			
EAN/UPC - Case	8711500062437			

Datasheet, 2023, April 30 data subject to change

EXC for SOX

Dimensional drawing



Product	D1	C1	A1	A2	B1
EXC 55 SOX 220-240V 50/60Hz	4.2 mm	28.0 mm	280.0 mm	265.0 mm	40.0 mm

