



PrimaVision Power for CDM

HID-PV C 150 /I CDM 220-240V 50/60Hz

PrimaVision Power gear is designed for optimal performance of 100 and 150 W CDM lamps – ideal where high-intensity light is key.



Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	350 mA
Inrush Current Width	0.50 ms
Inrush Current Peak (Max)	50 A
Number of Products on MCB (16A Type B) (Nom)	6
Wiring	
Cable Length From Device to Lamp	2.0 m
Connector Type	Insert
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Lifetime (Nom)	70 °C
T-Case Maximum (Max)	80 °C

Mechanical and Housing	
Housing	/I
Approval and Application	
Approval Marks	F-Marking CE marking ENEC certificate VDE-EMV certificate CB Certificate
Product Data	
Order product name	HID-PV C 150 /I CDM 220-240V 50/60Hz
Full product name	HID-PV C 150 /I CDM 220-240V 50/60Hz
Full product code	871150091287930
Order code	913700624466
Material Nr. (12NC)	913700624466
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500912879
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500912886

PrimaVision Power for CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV C 150 /1 CDM 220-240V 50/60Hz	4.8 mm	34.2 mm	223.9 mm	206.0 mm	82.7 mm

