



# Primaline Halogen Transformers

## PRIMALINE 70 230-240V 50/60HZ

High-Frequency electronic transformer for operation with 12V halogen lamps, available in 70W, 105W and 150W versions

### Warnings and Safety

- Transformer is not suitable for DC operation


### Product data

Operating and Electrical	
Input Voltage	230 to 240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Temperature	
T-case lifetime (nom.)	65 °C
T-Case maximum (max.)	80 °C
Approval and Application	
Approval marks	SELV CE marking ENEC certificate

Product Data	
Order product name	Primaline 70 230-240V 50/60Hz
Full product name	PRIMALINE 70 230-240V 50/60HZ
Full EOC	871150091266430
Order code	91266430
Material no. (12 NC)	913700627591
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500912664
Numerator – packs per outer box	50
EAN/UPC - Case	8711500912671

# Primaline Halogen Transformers

## Dimensional drawing



Product	C1	A1	B1
Primaline 70 230-240V 50/60Hz	33 mm	110 mm	45 mm

