



PrimaVision for CDM Elite MW

HID-PV 315 /S CDM 220-240V 50/60Hz


Highly reliable electronic drivers for medium-wattage lamps (210-400 W); designed to save energy via integrated one-step dimming and to reduce maintenance costs thanks to 80,000-hour lifetime and integrated lightning protection

Product data

Operating and Electrical		Environmental Standard	ISO 14001
Input Voltage	220 to 240 V	Approval Marks	CE marking ENEC certificate CB Certificate
Line Frequency	50 to 60 Hz	Product Data	
Input Frequency	50 to 60 Hz	Order product name	HID-PV 315 /S CDM 220-240V 50/60Hz
Earth Leakage Current (Max)	0.5 mA	Full product name	HID-PV 315 /S CDM 220-240V 50/60Hz
Input Current (Nom)	1.53 A	Full product code	872790084311800
Number of Products on MCB (16A Type B) (Nom)	4	Local code description	HID-PV 315 /S CDM 220-240V 50/60Hz
Wiring		Order code	913700639466
Connector Type	Insert	Material Nr. (12NC)	913700639466
Temperature		Local order code	HID-PV315/SCDM
Ambient temperature range	-20 °C to 55 °C	Numerator - Quantity Per Pack	1
Mechanical and Housing		EAN/UPC - Product/Case	8711500880888
Housing	/S	Numerator - Packs per outer box	4
Approval and Application		EAN/UPC - Case	8727900843118
Safety Standard	EN60928, 60926		

PrimaVision for CDM Elite MW

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV 315 /S CDM 220-240V 50/60Hz	4.2 mm	60.0 mm	215.0 mm	204.5 mm	128.5 mm	111.5 mm

