

PrimaVision Mini for CDM

HID-PV m 20 /I CDM HPF 220-240V 50/60Hz

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.5 mA
Inrush Current Width	0.25 ms
Inrush Current Peak (Max)	15 A
Number of Products on MCB (16A Type B) (Nom)	24
Wiring	
Cable Length From Device to Lamp	2 m
Connector Type	Insert
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Lifetime (Nom)	75 °C
T-Case Maximum (Max)	75 °C
Mechanical and Housing	
Housing	Independent

Approval and Application	
Approval Marks	F-Marking CE marking ENEC certificate CB Certificate
Product Data	
Order product name	HID-PV m 20 /I CDM 220-240V 50/60Hz
Full product name	HID-PV m 20 /I CDM HPF 220-240V 50/60Hz
Full product code	872790089060000
Order code	89060000
Material Nr. (12NC)	913700646266
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500881632
Numerator - Packs per outer box	10
EAN/UPC - Case	8727900890600

PrimaVision Mini for CDM

Dimensional drawing



Product	D1	C1	A1	A2	A3	B1
HID-PV m 20 /I CDM 220-240V 50/60Hz	4.8 mm	34.0 mm	234.7 mm	225.1 mm	202.0 mm	49.4 mm

