



# PrimaVision Mini for CDM

## HID-PV m 20 /I CDM HPF 220-240V 50/60Hz

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design


### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Earth leakage current (max.)	0.5 mA
Inrush current width	0.25 ms
Inrush current peak (max.)	15 A
Number of products on MCB (16 A type B) (nom.)	24
Wiring	
Cable length from device to lamp	2 m
Connector type	Insert
Temperature	
Ambient temperature range	-20°C to 45°C
T-case lifetime (nom.)	75 °C
T-Case maximum (max.)	75 °C
Mechanical and Housing	
Housing	Independent

Approval and Application	
Approval marks	F-Marking CE marking ENEC certificate CB certificate
Product Data	
Order product name	HID-PV m 20 /I CDM 220-240V 50/60Hz
Full product name	HID-PV m 20 /I CDM HPF 220-240V 50/60Hz
Full EOC	872790089060000
Order code	89060000
Material no. (12 NC)	913700646266
Local order code	PVM20IHPF
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500881632
Numerator – packs per outer box	10
EAN/UPC - Case	8727900890600

# PrimaVision Mini for CDM

## Dimensional drawing



Product	D1	C1	A1	A2	A3	B1
HID-PV m 20 /I CDM 220-240V 50/60Hz	4.8 mm	34.0 mm	234.7 mm	225.1 mm	202.0 mm	49.4 mm

