

PrimaVision Compact for CDM

HID-PV C 70 /I CDM 220-240V 50/60Hz NG

High-quality, compact and lightweight HID electronic gear for optimal and reliable performance of 20, 35, 50 and 70 W CDM lamps


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.25 mA
Inrush Current Width	0.33 ms
Inrush Current Peak (Max)	33 A
Number of Products on MCB (16A Type B) (Nom)	20
Wiring	
Cable Length From Device to Lamp	2.0 m
Connector Type	Insert
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Lifetime (Nom)	75 °C
T-Case Maximum (Max)	75 °C
Mechanical and Housing	
Housing	/I

Approval and Application	
Safety Standard	EN 61347-2-12
Environmental Standard	ISO 14001
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	HID-PV C 70 /I CDM 220-240V 50/60Hz NG
Full product name	HID-PV C 70 /I CDM 220-240V 50/60Hz NG
Full product code	872790085988100
Local code description	HID-PV C 70 /I CDM 220-240V 50/60Hz NG
Order code	913700653266
Material Nr. (12NC)	913700653266
Local order code	HIDPVC70/I CDM
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500881717
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900859881

PrimaVision Compact for CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV C 70 /I CDM 220-240V 50/60Hz NG	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm

